

TECHSPEC® 50mm Dia. x 100mm FL, VIS 0° Coated, Achromatic Lens



Stock **#49-284** ☐ In Stock
[Other Coating Options](#)

1 **C\$252.00**

ADD TO CART

Qty 1-5
C\$252.00
Qty 6+
C\$201.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):
100.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 89.94
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 49.00
Centering (arcmin): <1
Center Thickness CT (mm): 17.92 ±0.20
Center Thickness CT 1 (mm): 13.92 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R₁ (mm): 69.28
Radius R₂ (mm): -46.95
Radius R₃ (mm): -446.01
Edge Thickness ET (mm): 12.55
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View