

TECHSPEC® 5.0mm Dia. x 12.0mm FL, VIS-NIR, Inked, Plano-Convex Lens



Stock **#47-859-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 +

C\$81.90

ADD TO CART

Qty 1-9
C\$81.90
Qty 10+
C\$73.85
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 ±0.025

Effective Focal Length EFL (mm):
12.00 @ 587.6nm

Back Focal Length BFL (mm): 10.83
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.77 ±0.05
Edge Thickness ET (mm): 1.25
Radius R₁ (mm): 6.22
Clear Aperture CA (mm): 4.5
f#: 2.4
Numerical Aperture NA: 0.21
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View