

TECHSPEC® 50mm Protected Silver Coated, N-BK7 Right Angle Mirror



Stock **#89-634** ☐ In Stock

1 **C\$402.50**

ADD TO CART

Qty 1-5
C\$402.50
Qty 6+
C\$322.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[N-BK7](#)

Surface Quality:
60-40

Length of Legs (mm):

50.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 63.64 x 45.00
Length of Hypotenuse (mm): 70.70
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant