

50μm 0.22 NA UV/VIS Fiber, 10m Length



Stock **#57-066** ☐ In Stock

-

1

+

C\$81.20

ADD TO CART

Qty 1-4
C\$81.20
Qty 5+
C\$71.40
Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°): 25.4
Buffer Material: Polyimide
Cladding Diameter (μm): 125 +1/-3

Coating: UVMS
Minimum Bend Radius (mm): 25/13 (Continuous/Momentary)
Substrate: Fused Silica (Corning 7980)
Length (m): 10.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 145 ±5
Core Diameter (µm): 50 ±2
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.439
Wavelength Range (nm): 190 - 1250
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View