

[See all 11 Products in Family](#)

## 50mW, 635nm Fiber-Coupled Laser Module



Stock #19-482 **5 In Stock**

C\$1,155<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | C\$1,155.00 each              |
| Qty 10+        | C\$1,039.50 each              |
| Need More?     | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads



### General

**Type of Laser:**  
 Diode

**Laser Class - CDRH:**  
 Class IIIb

### Physical & Mechanical Properties

**Length of Fiber (m):**  
 1

151.00 Length (mm):

## Optical Properties

Fiber-Coupled Spatial Mode:

635.00 ±5 Wavelength (nm):

Red Color:

## Electrical

50 Output Power (mW):

## Hardware & Interface Connectivity

5.0 Operating Voltage (V):

Fiber-Coupled Output Type:

SMA Connector:

## Environmental & Durability Factors

+15 to +30 Operating Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 233:

## Product Details

- 400µm Core Multimode Fiber with SMA Connector
- 50 and 100mW Output Power Options
- VIS and NIR Wavelengths Available
- [Free Space Alignment Lasers](#) Also Available

Fiber-Coupled Laser Modules feature an integrated 1m long, 400µm core fiber with an SMA905 connector. These cost-effective lasers provide up to 100mW of output power and have a long expected lifetime of 5000 hours. Fiber-Coupled Laser Modules are ideal for use in laser alignment, laser pointing, and laser measurement applications where a free-spaced laser diode module may be difficult to position. These lasers' compact size and easy operation make them well suited for integration into OEM systems.

**Note:** Power supply is sold separately.