

TECHSPEC® 50mm Dia. x 250mm FL, VIS-NIR Coated, Double-Convex Lens



Stock **#45-909** ☐ In Stock
[Other Coating Options](#)

1 **C\$101.50**

ADD TO CART

Qty 1-9
C\$101.50
Qty 10+
C\$91.35
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Back Focal Length BFL (mm):
248.37

Effective Focal Length EFL (mm): 250.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.93
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.50
Radius R₁=R₂ (mm): 257.57
Clear Aperture CA (mm): 49.00
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant