

50mW, 808nm LC Turnkey Laser



Low Cost Turnkey Laser & Power Supply (Included)



Stock **#19-489** **2 In Stock**

-

1

+

C\$5,716²⁷

ADD TO CART

Volume Pricing	
Qty 1+	C\$5,716.27 each
Need More?	Request Quote

Product Downloads



SPECIFICATIONS

General

<5	Warm-Up Time (minutes):
Diode	Type of Laser:

IIIb	Laser Class - CDRH:
10000	Mean Time to Failure MTTF (hours):
Physical & Mechanical Properties	
<0.05	Pointing Stability after Warm Up (mrad°C):
143.5 x 73.0 x 46.2	Dimensions (mm):
24.8	Beam Height from Base Plate (mm):
Optical Properties	
>50:1	Polarization:
808.00	Wavelength (nm):
±3	Wavelength Tolerance (nm):
3.5	Beam Diameter (mm):
<1.0	Beam Divergence (mrad):
Infrared	Color:
Electrical	
50	Output Power (mW):
<2% RMS over 4 hours	Power Stability (%):
1	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
162 x 144 x 70	Power Supply:
100-240VAC	Power Requirement:
Free Space	Output Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Multiple Colors and Wavelengths Available
- Ideal for Microscopy Applications
- TE Cooled

Low Cost Turnkey Lasers offer excellent beam quality and output powers up to 50mW. These lasers feature compact designs for simplified integration and manually adjustable output power through the control box. Each laser features TE cooling and flexible interface allowing for digital or analog modulation, with multiple color and wavelength options available. Low Cost Turnkey Lasers are ideal for research, flow cytometry, and microscope illumination applications.

Note: Power supply included. Fiber-coupled lasers include 1m SMA905 coupled fiber.

TECHNICAL INFORMATION

