

[See all 22 Products in Family](#)

50mm Dia. x 25mm FL Protected Gold, Concave Mirror



Stock #43-839 **15 In Stock**

⊖ 1 ⊕ C\$112.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-49	C\$112.00 each
Qty 50-99	C\$95.20 each
Need More?	Request Quote

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

±0.5 **Thickness Tolerance (mm):**

50.00 ±0.50 **Diameter (mm):**

90 **Clear Aperture (%):**

Edge Thickness ET (mm):

6.0

Optical Properties

Coating Type:
Metal

Coating:
Protected Gold (700-10000nm)

Wavelength Range (nm):
700 - 10000

Effective Focal Length EFL (mm):
25.00

Substrate:
N-BK7

Aperture (f/#):
f/0.5

Coating Specification:
R_{avg} >96% @ 700 - 2000nm
R_{avg} >96% @ 2000 - 10,000nm

Focal Length Tolerance (%):
±2

Radius R₁ (mm):
50.00

Surface Quality:
80-50

Radius of Curvature (mm):
50.00

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

Technical Information

