

TECHSPEC®

50mm H x 25mm L x 100mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens



Stock #69-763 ☒ In Stock

-

1

+

C\$180.60

ADD TO CART

Qty 1-5
C\$180.60
Qty 6+
C\$144.20
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate:
[N-BK7](#)

f/#:
2

Numerical Aperture NA: 0.25
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): 94.93
Center Thickness CT (mm): 7.70
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 50.0 x 25.0
Edge Thickness ET (mm): 1.28
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant