

TECHSPEC® 50mm, Protected Silver Coated, N-BK7 90° Specialty Mirror



Stock **#21-190** [CONTACT US](#)

- 1 + **C\$525.00**

ADD TO CART

Qty 1-5
C\$525.00
Qty 6+
C\$420.00
Volume Pricing
Request Quote

Get Product Downloads



Clear Aperture CA (mm):
49.0

Coating:
Protected Silver (450-10000nm)

Substrate: [N-BK7](#)

Surface Quality:

40-20
Type: Right Angle Mirror
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture (%): 90.00
Length of Hypotenuse (mm): 70.70
Length of Legs (mm): 50.00
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Wavelength Range (nm): 450 - 10000
Coating Type: Metal
Damage Threshold, Reference: ☐ 0.5 J/cm ² @ 532nm & 1064nm, 10ns
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant