

TECHSPEC® 50mm, VIS 0° Coated, Rhomboid Prism



Stock **#49-423** ☐ In Stock

-

1

+

C\$546.00

ADD TO CART

Qty 1-5
C\$546.00
Qty 6+
C\$436.80
Volume Pricing
Request Quote

Get Product Downloads



Length (mm):
50.00

Coating:
VIS 0° (425-675nm)

Angle Tolerance (arcsec):
±5

Beam Deviation (arcsec):

±30
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): ±0.1
Image Orientation: Beam Deviation
Ray Deviation (°): 0.00
Substrate: □ N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Rhomboid Prism
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: □ Entrance/Exit Surfaces: 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View