

50µm 0.22 NA UV/VIS Fiber, 25m Length



Stock **#57-072** ☐ In Stock

-

1

+

C\$203.00

ADD TO CART

Qty 1-4
C\$203.00
Qty 5+
C\$179.20
Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°): 25.4
Buffer Material: Polyimide
Cladding Diameter (µm): 125 +1/-3

Coating: UVMS
Minimum Bend Radius (mm): 25/13 (Continuous/Momentary)
Substrate: Fused Silica (Corning 7980)
Length (m): 25.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 145 ±5
Core Diameter (µm): 50 ±2
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.439
Wavelength Range (nm): 190 - 1250
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View