

TECHSPEC® 5mm Dia. x 15mm FL, YAG-BBAR Coated, Inked, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-213-INK** 3-5 DAYS

- 1 +

C\$86.80

ADD TO CART

Qty 1-9
C\$86.80
Qty 10+
C\$78.05
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 ±0.025

Back Focal Length BFL (mm):
14.33

Effective Focal Length EFL (mm): 15.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate:  N-BK7
Surface Quality: 40-20
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.58
Radius R₁=R₂ (mm): 15.16
Clear Aperture CA (mm): 4.50
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View