

[See all 16 Products in Family](#)

5.0mW 633nm, LDM Focusable Laser Diode (Recertified 05-P)



Stock #53-756-RCD-05P **RECERTIFIED** 1 In Stock

- 1 + C\$192.⁸²

ADD TO CART

Volume Pricing

Qty 1+	C\$192.82 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Index Guided Diode, CW **Type:**

Mean Time To Failures MTTF @ 25° (hours):
≥30,000

Fully shielded, reverse polarity protected **Drive Circuitry:**

Includes: Users Manual, Warning Label, and Focus Key **Note:**

Diode **Type of Laser:**

Illa **Laser Class - CDRH:**

Physical & Mechanical Properties

22.00 **Weight (g):**

≤20 **Pointing Accuracy (mrad):**

215 **Length of Leads (mm):**

34.00 **Length (mm):**

Optical Properties

635.00 **Wavelength (nm):**

±8 **Wavelength Tolerance (nm):**

0.25 **Wavelength Stability (nm/°C):**

<0.525 **Beam Size at Nearest Focus (µm):**

4 x 2 at Aperture **Beam Diameter (mm):**

<0.5 **Beam Divergence (mrad):**

Red **Color:**

35mm - ∞ **Focus Range (mm):**

Electrical

4.5 (Maximum) **Output Power (mW):**

±5 **Output Power Tolerance (%):**

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately:
USA: [#59-099](#)
Europe: Not Available
Japan: [#59-099](#)
Korea: Not Available
China: [#59-099](#)

3.5 - 5 VDC **Power Requirement:**

red (+), black (-) **Electrical Leads/ Pin Connections:**

Free Space **Output Type:**

Environmental & Durability Factors

-10 to +45 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Product Details

- Circular and Elliptical Beam Options
- Bare Leads for Instrument Integration
- Focusable from 20mm to Infinity

Compact LDMFocusable Laser Diode Modules are self-contained and compact and offer a variety of features. They are an ideal replacement for a helium-neon laser in many applications and offer the benefits of superior durability, small size, and a range of wavelengths and powers. Elliptical output beams are produced using a user-adjustable glass focusing lens. Circular output beams are produced using a long focal length plastic lens and are suitable for long-distance and alignment applications. Compact LDMFocusable Laser Diode Modules applications include use as pilot beams for alignment, bar code readers, measurement, dimensional scanning, robotic control, target designation, positioning, and analysis. There is a focusing tool included with all diode modules. Line Generator attachments are available and sold separately for all diode modules listed. [Power Supply](#) is required for operation and is sold separately.

Note: The laser diode case is electrically isolated from the supply voltage.

Technical Information

