

[See all 6 Products in Family](#)

**TECHSPEC® 515, 1030nm, 12.7mm Dia., Dual Band Low GDD Mirror**



Stock #17-286 **20+ In Stock**

- 1 + C\$249<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$249.20 each
Qty 6-9	C\$221.20 each
Qty 10+	C\$197.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**

**Typical Applications:**  
Beam transport of 1st and 2nd harmonic of Yb:doped lasers

**Physical & Mechanical Properties**

Parallelism (arcmin):  
<3

>86	<b>Clear Aperture (%):</b>
Commercial Polish	<b>Back Surface:</b>
12.70 +0/-0.1	<b>Diameter (mm):</b>
6.35 ±0.20	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
10-5	<b>Surface Quality:</b>
R <sub>s</sub> >99.9% @500-540nm R <sub>p</sub> >99.8% @507-527nm R <sub>s</sub> >99.9% @1000-1070nm R <sub>p</sub> >99.8% @1005-1070nm	<b>Coating Specification:</b>
<35fs <sup>2</sup> @ 500 - 540nm (s-pol) <50fs <sup>2</sup> @ 510 - 525nm (p-pol) <20fs <sup>2</sup> @ 1000 - 1070nm (s-pol) <40fs <sup>2</sup> @ 1010 - 1055nm (p-pol)	<b>GDD Specification:</b>
500 - 540, 1000 - 1070	<b>Wavelength Range (nm):</b>
<λ/8 @ 632.8nm over 9mm aperture	<b>Surface Flatness (P-V):</b>
S1: Dielectric S2: Stress-compensating	<b>Coating Type:</b>
Ultrafast (500-540, 1000-1070nm)	<b>Coating:</b>
515, 1030	<b>Design Wavelength DWL (nm):</b>
45	<b>Angle of Incidence (°):</b>
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- High Reflectivity & Low Group Delay Dispersion (GDD) for Ultrafast Beam Steering
- Ion-Beam Sputtered (IBS) Coatings Minimize Scatter and Absorption Losses
- Near-Zero GDD for Both the First and Second Harmonics of Ti:sapphire and Yb-doped Lasers

TECHSPEC® Dual Band Low GDD Ultrafast Mirrors maintain high reflectivity and near-zero group delay dispersion over both the first and second harmonic of Ti:sapphire and Yb-doped lasers. Utilizing Ion-Beam Sputtered Coating Technology, these mirrors minimize scatter and absorption loss commonly observed when using other traditional coating application processes. TECHSPEC® Dual Band Low GDD Ultrafast Mirrors are often used in beam steering applications as they will maintain ultrashort pulse durations that can be difficult to preserve when using more conventional laser mirrors. These mirrors are ideal for second-harmonic generation (SHG) microscopy and spectroscopy applications as well as for frequency resolved optical gating (FROG).

## Compatible Mounts