

TECHSPEC® 5mm Dia. x 4mm FL, NIR I Coated, Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#15-727** ☐ **In Stock**

[Other Coating Options](#)

1

C\$74.20

ADD TO CART

Qty 1-10

C\$74.20

Qty 11+

C\$65.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.2

Effective Focal Length EFL (mm):
4.00 @ 587.6nm

Numerical Aperture NA:
0.625

Back Focal Length BFL (mm): 1.45
Substrate: ☐ Liba2000+
Focal Length Tolerance (%): ±5
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 4.35
Edge Thickness ET (mm): 2.14
Center Thickness CT (mm): 3.88 ±0.30
f#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 5.00
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant