

TECHSPEC® 532nm 2X - 8X Research-Grade Variable Beam Expander



Research-Grade Variable Beam Expanders



Stock **#87-567** CLEARANCE ☐ In Stock

⊖ 1 ⊕

C\$2,303.00

ADD TO CART

Qty 1-4

C\$2,303.00

Qty 5+

C\$2,037.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0 ±0.06

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm): 532
Entrance Aperture (mm): 15
Exit Aperture (mm): 30
Expansion Power: 2X - 8X
Substrate: Fused Silica (Corning 7980)
Length (mm): 169.00
Mounting Threads: Input: Male C-Thread (1" x 32 TPI) Output: Male T-Thread (M42 x 0.75)
Transmission (%): >97.5 @ DWL
Type: Beam Expander
Weight (g): 501
Housing Diameter (mm): 51
Transmitted Wavefront, P-V: <λ/4 @ 532nm for Input Beam ≤4mm (2X-6X) <λ/4 @ 532nm for Input Beam ≤2mm (>6X)
Coating Specification: R_{abs} <0.25% @ 531 - 533nm R_{avg} <0.5% @ 510 - 555nm
Wavelength Range (nm): 510 - 555
Style: Variable Magnification
Damage Threshold, By Design: 5 J/cm² (>3X), 3 J/cm² (2-3X) @ 10ns, 20 Hz, 532nm
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View