

TECHSPEC® 5mm λ/20, 266nm V-Coat, Nd:YAG Right Angle Prism



TECHSPEC Nd:YAG Laser Line λ/20 UV Fused Silica Right Angle Prisms

Stock **#37-616** ☐ In Stock

-

1

+

C\$403.20

ADD TO CART

Qty 1-5

C\$403.20

Qty 6+

C\$322.70

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Laser V-Coat (266nm)

Design Wavelength DWL (nm):
266

Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 7.10
Length of Legs (mm): 5.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: R_{abs} <0.25% @ 266nm
Surface Flatness (P-V): λ/20
Damage Threshold, By Design: 3 J/cm², 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View