

[See all 34 Products in Family](#)

5mW, 850nm Alignment Laser Diode (Recertified 05-P)



Red and IR Alignment Laser Diode

Stock **#37-039-RCD-05P** RECERTIFIED **1 In Stock**

⊖ 1 ⊕ C\$210⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$210.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

IIIb **Laser Class - CDRH:**

Physical & Mechanical Properties

36.00 **Length (mm):**

Optical Properties

Wavelength (nm):

850.00

Wavelength Tolerance (nm):

±5

Beam Diameter (mm):

3 x 1 Typical

Beam Divergence (mrad):

Major Axis: 0.5
Minor Axis: 0.2

Color:

Infrared

Electrical

Output Power (mW):

5

Modulation Frequency (kHz):

0 - 10

Hardware & Interface Connectivity

Operating Voltage (V):

5

Power Supply:

Power Supply Required and Sold Separately:

USA: [#73-818](#)

Europe: [#73-818](#)

Japan: [#13-640](#)

Korea: [#33-770](#)

China: [#73-818](#)

Environmental & Durability Factors

Operating Temperature (°C):

-10 to 50

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Focus Adjustable
- TTL Modulation up to 10kHz
- 635nm, 780nm, 808nm, 850nm, and 980nm Wavelength Options

Red and IR Alignment Laser Diodes are available in output powers from 1 to 100mW at 635nm, 780nm, 808nm, 850nm, and 980nm wavelengths. These low cost laser diode modules combine drive electronics and beam collimating optics, making them ideal for OEM integration applications. Red and IR Alignment Laser Diodes feature TTL Modulation up to 10kHz and are best utilized in alignment applications or systems with simple detectors.

Note: Power supply and mounting bracket are sold separately.