

## 3W Deuterium/3W Tungsten Lamp Source (UV-VIS-NIR Range)



3W Deuterium/3W Tungsten Lamp Source (UV-VIS-NIR Range), #57-055

Stock **#57-055** **1 In Stock**

⊖ 1 ⊕ C\$4,193.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$4,193.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**  
External power supply and AC cord included. Fiber patchcord listed under Accessories tab sold separately.

**Lamp Lifetime (hours):**  
≥1000 / ≥2000

### Physical & Mechanical Properties

**Dimensions (mm):**  
171 x 76 x 64

## Optical Properties

Wavelength Range (nm):  
200 - 1100

## Electrical

Output Power (W):  
3W Deuterium, 3W Tungsten, 6W Both

## Hardware & Interface Connectivity

Connector:  
SMA-905

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- Designed for Use with [Spectrometers](#)
- Lamps Available for UV to NIR
- Xenon, Tungsten, or Deuterium Sources

Broadband Fiber-Coupled Light Sources are ideal for use in a variety of spectroscopy applications and for coupling with the Fiber Optic Reflectance Sphere. The pulsed Xenon source is designed for applications from the UV to visible. The Tungsten source is designed for applications in the visible to NIR. The Deuterium/Tungsten source is ideal for applications requiring wide spectral ranges from the UV to NIR.