

TECHSPEC® 577 & 690nm, 25mm Dia., Dual-Band Filter



Multi-Band Fluorescence Bandpass Filters

Stock **#87-243** ☐ In Stock



1



C\$583.80

ADD TO CART

Qty 1-9

C\$583.80

Qty 10+

C\$487.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0

Bandwidth (nm):
24 @ 577nm
50 @ 690nm

Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 21.34
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Transmission (%): >90
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Mounted in Black Anodized Ring
Compatible Fluorophore: CY3 & CY5 Emission
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.00 ±0.25
Multi-Band Center Wavelengths (nm): 577, 690

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant