

## TECHSPEC® 6" Diameter x 36" FL Uncoated, Parabolic Mirror



Stock #32-071-000  In Stock

1  **C\$848.40**

**ADD TO CART**

Qty 1-4

C\$848.40

Qty 5+

C\$721.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate:   
**BOROFLOAT®**

Focal Length Tolerance (%):  
±1.5

Surface Quality:  
60-40

Surface Accuracy:

N8

**Diameter (inches):**

6.0 +0.06/-0

**Diameter (mm):**

152.40 +1.5/-0

**Effective Focal Length EFL (inches):**

36.0

**Effective Focal Length EFL (mm):**

914.40

**Radius of Curvature (mm):**

1,828.80

**Aperture (f#):**

f/6

**Coating:**

Uncoated

**Coating Type:**

Uncoated

**Back Surface:**

Ground

**Clear Aperture CA (mm):**

138

**Edge Thickness ET (inches):**

1.00

**Edge Thickness ET (mm):**

25.40

**Type:**

Parabolic Mirror

## Regulatory Compliance

**RoHS:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

---