


[See all 19 Products in Family](#)

6 x 6 x 0.2mm, 1030nm SHG, Type I BBO Nonlinear Crystal



Stock **#24-196** **5 In Stock**

-

1

+

C\$1,078^{.00}

ADD TO CART

Volume Pricing	
Qty 1-2	C\$1,078.00 each
Qty 3+	C\$959.00 each
Need More?	Request Quote

Product Downloads

General	
Nonlinear Crystal	Type:
SHG @ 1030 nm, Type I	Typical Applications:
Mount is 25.4mm Dia. 6mm Thick Unthreaded Black Anodized Metal Mount (see drawing for more information)	Note:
BBO	Crystal Type:

<0.1 mm x45°	Protective Chamfer:
Physical & Mechanical Properties	
6.0 x6.0 +0.0/-0.1	Dimensions (mm):
0.20 +0.0/-0.03	Thickness (mm):
>5	Clear Aperture CA (mm):
<20	Parallelism (arcsec):
<5	Perpendicularity (arcmin):
Optical Properties	
20-10	Surface Quality:
AR Coating	Coating:
1030	Design Wavelength DWL (nm):
$\lambda/4$ @ 632.8nm	Surface Flatness (P-V):
Coating Specification: S1: 515 & 1030nm AR Coating S2: 515 & 1030nm AR Coating	
Damage Threshold, By Design: ☐ >1 GW/cm ² @ 1064nm, 10ns	
Damage Threshold, Pulsed: >1 GW/cm ² @ 1064nm, 10ns	
23.4/90	Orientation Θ/Φ (°):
Threading & Mounting	
Mounted	Mount:
6 (unthreaded)	Mount Thickness (mm):
25.4	Mount Diameter (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- BBO Crystals for Frequency Conversion of 800nm and 1030nm Lasers
- LBO Crystals for Frequency Conversion of 1030nm and 1064nm Lasers
- High Damage Thresholds Up to 10 J/cm² @ 1064nm, 10ns, 10Hz
- Broad Transparency Range from the UV to the IR

Nonlinear Crystals of either β -barium borate (BBO) or lithium triborate (LBO) are used for frequency conversion of laser sources. BBO crystals feature thicknesses from 0.2mm to 0.5mm to minimize group velocity mismatch and are ideal for frequency doubling or tripling of Ti:Sapphire and Yb:doped laser pulses. The critical and noncritical phase matching LBO crystals are ideal for second or third harmonic generation of Nd:YAG and Yb:doped lasers. Nonlinear Crystals with 20-10 surface quality and $\lambda/10$ (LBO) or $\lambda/8$ (BBO) surface flatness provide the broad transparency range and large nonlinear coefficient needed for the harmonic generation of fundamental laser frequencies. Each crystal features a protective anti-reflection (AR) coating that minimizes reflection and limits fogging from ambient conditions.