

TECHSPEC®

600 x 1000mm High-Temperature Linear Polarizing Film (XP40HT-40)



High-Temperature Linear Polarizing Film (XP40HT)

Stock #14-348 CLEARANCE ☐ In Stock

-

1

+

C\$366.73

ADD TO CART

Qty 1+

C\$366.73

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:
Uncoated, Protective Film on Both Sides

Extinction Ratio:
5000:1

Substrate: ☐
[Polymer Film XP40HT-40](#)

Dimensions (mm):
600.0 x 1000.0

Thickness (mm):
0.40 ±0.05

Transmission (%) Single: 40 ±2 Parallel: 32.2 Crossed: <0.005
Type: Linear Polarizer
Dimensional Tolerance (mm): +0/-3
Construction: Polarizing Film
Note: Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.99
Heat Resistance (°C x Hours): 100 x 1,000
Cold Resistance (°C x Hours): -40 x 1,000
Humidity Resistance (°C x Hours): 80 x 90% RH x 1,000
Transmission Variance after 1000 Hours (%): <±10
#Sorting: 45.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)