

600µm 0.22 NA VIS/NIR Fiber, 10m Length



Stock **#57-088** ☐ In Stock

-

1

+

C\$651.00

ADD TO CART

Qty 1-4
C\$651.00
Qty 5+
C\$574.00
Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°):
25.4

Buffer Material:
Polyimide

Cladding Diameter (µm):
660 ±13.2

Coating: VS/NIR
Minimum Bend Radius (mm): 132/66 (Continuous/Momentary)
Substrate: Fused Silica (Corning 7980)
Length (m): 10.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 710 ±5
Core Diameter (µm): 600 ±12
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.440
Wavelength Range (nm): 300 - 2400
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View