

TECHSPEC®

6.0mm Dia. x 7.5mm FL, NIR I Coated, Plano-Convex Lens



Stock **#49-904** ☐ In Stock
[Other Coating Options](#)

1

C\$53.20

ADD TO CART

Qty 1-9
C\$53.20
Qty 10+
C\$47.95
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):
7.50 @ 587.6nm

Back Focal Length BFL (mm): 6.10
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 2.50 ±0.05
Edge Thickness ET (mm): 1.68
Radius R₁ (mm): 5.89
Clear Aperture CA (mm): 5.4
f/#: 1.25
Numerical Aperture NA: 0.40
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View