


**TECHSPEC® 5mm VIS 0° Coated, BBAR Coated Right Angle Prism**



Stock **#84-505** ☐ In Stock

-

1

+

**C\$148.40**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$148.40                     |
| Qty 6+                        |
| C\$119.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Angle Tolerance (arcsec):  
±15

Coating:  
VIS 0° (425-675nm)

Substrate: ☐  
[N-BK7](#)

Surface Quality:

|                                                                                                                        |
|------------------------------------------------------------------------------------------------------------------------|
| 40-20                                                                                                                  |
| <b>Type:</b><br>Right Angle Prism                                                                                      |
| <b>Dimensional Tolerance (mm):</b><br>+0.00/-0.10                                                                      |
| <b>Bevel:</b><br>Protective bevel as needed                                                                            |
| <b>Clear Aperture (%):</b><br>90                                                                                       |
| <b>Length of Hypotenuse (mm):</b><br>7.10                                                                              |
| <b>Length of Legs (mm):</b><br>5.00                                                                                    |
| <b>Image Orientation:</b><br>Left-Handed                                                                               |
| <b>Note:</b><br>Coating on Entrance/Exit Faces                                                                         |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                                                  |
| <b>Ray Deviation (°):</b><br>90                                                                                        |
| <b>Wavelength Range (nm):</b><br>425 - 675                                                                             |
| <b>Surface Flatness (P-V):</b><br>λ/8                                                                                  |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>Entrance/Exit Faces: 5 J/cm <sup>2</sup> @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |