

TECHSPEC® 6.25mm Dia. x 60mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-698** ☐ In Stock
[Other Coating Options](#)

1 **C\$93.80**

ADD TO CART

Qty 1-5
C\$93.80
Qty 6+
C\$74.90
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):
60.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 58.46
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 5.625
Centering (arcmin) : <1
Center Thickness CT (mm) : 3.30 ±0.10
Center Thickness CT 1 (mm) : 2.30 ±0.05
Center Thickness CT 2 (mm) : 1.00 ±0.05
Radius R₁ (mm) : 37.16
Radius R₂ (mm) : -26.28
Radius R₃ (mm) : -76.48
Edge Thickness ET (mm) : 3.10
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 9.6
Numerical Aperture NA : 0.05
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View