

TECHSPEC® 6.25mm Dia. x 7.5mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-948** ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$100.80

ADD TO CART

Qty 1-5
C\$100.80
Qty 6+
C\$80.50
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):
7.50

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 4.45
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <3
Center Thickness CT (mm): 6.00 ±0.10
Center Thickness CT 1 (mm): 5.00 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R₁ (mm): 5.60
Radius R₂ (mm): -3.71
Radius R₃ (mm): -11.34
Edge Thickness ET (mm): 4.61
Substrate: ☐ N-BAF10 / N-SF57
Surface Quality: 40-20
f/#: 1.2
Numerical Aperture NA: 0.42
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View