


TECHSPEC®


6.0mm Dia. x -12 FL, 1064nm V-Coat, UV Plano-Concave Lens



Stock #21-027 **3 In Stock**

1 C\$203.⁰⁰

ADD TO CART



Volume Pricing	
Qty 1-5	C\$203.00 each
Qty 6-25	C\$162.40 each
Qty 26-49	C\$151.20 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
Curve (xlsx):xlsx	
Zemax:zmx	eDrawing:eprt
EO Spec Sheet	Download All

General

Type: Plano-Concave Lens

Note: Max. Flat Annulus is 0.3mm

Physical & Mechanical Properties

Diameter (mm): 6.00
+0.0/-0.025

Center Thickness CT (mm): 2.00

Center Thickness Tolerance (mm): ±0.05

Centering (arcmin): <1

Clear Aperture CA (mm): 5.4

Edge Thickness ET (mm): 2.71

Optical Properties

Effective Focal Length EFL (mm): -12.00

Substrate: **Fused Silica**
(Corning 7980)

f/#: 2.00

Numerical Aperture NA: 0.25

Coating: 1064nm V-Coat

Back Focal Length BFL (mm): -13.38

Coating Specification: R_{abs} <0.25% @ 1064nm

Design Wavelength DWL (nm): 1064

Focal Length Specification Wavelength (nm): 587.6

Focal Length Tolerance (%): ±1

Radius R₁ (mm): -5.50

Surface Quality: 40-20

Damage Threshold, By Design: ⓘ	15 J/cm ² @ 1064nm, 10ns	Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4		

Regulatory Compliance

Certificate of Conformance: [View](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Negative Focal Lengths for Beam Expansion or Light Projection Applications
- Research-Grade Synthetic Fused Silica Substrate
- <0.25% Reflection at 1064nm for Nd:YAG and Fiber Laser Applications
- **Uncoated and BBAR Coating Options** Available

TECHSPEC® 1064nm Laser Line Coated UV Fused Silica Plano-Concave (PCV) Lenses are high performance lenses that feature a low coefficient of thermal expansion. Manufactured using research-grade synthetic fused silica, these lenses provide excellent transmission and chemical purity. TECHSPEC® 1064nm Laser Line Coated UV Fused Silica Plano-Concave (PCV) Lenses are designed for maximum throughput at 1064nm, making them ideal for applications utilizing Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.

Related Products



UV Fused Silica Plano-Concave (PCV) Lenses



Uncoated Double-Concave (DCV) Lenses



Optical Lens and Filter Mounts



Laser Lenses

Frequently Purchased Together



#55-155 - Preloaded Norland Optical Adhesive NOA 61 Dispensing Barrel (3cc)
C\$41.25

Qty



#65-533 - 6.0mm Diameter x 30.0mm FL, 1064nm V-Coat, PCX Lens
C\$68.60

Qty



#69-591 - 6.0mm Diameter x 48.0mm FL, 1064nm V-Coat, PCX Lens
C\$69.30

Qty












#69-592 - 6.0mm Diameter x 60.0mm FL, 1064nm V-Coat, PCX Lens
C\$69.30

Qty



Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
 	6.0mm Optic Dia., Optic Mount	Fixed		#64-552	C\$45.85 Request Quote	2 In Stock <input type="text" value="1"/> 
 	6mm Inner Single Optic Mount	Fixed		#38-745	C\$57.40 Request Quote	20+ In Stock <input type="text" value="1"/> 
 	25mm Cage 6mm Diameter Lens Mount	Fixed		#85-554	C\$64.05 Request Quote	1 In Stock <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).