

LightPath 355230 | 633nm Alignment, 0.55 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#67-723** ☐ In Stock

1

C\$252.00

ADD TO CART

Qty 1-10
C\$252.00
Qty 11+
C\$221.90
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
4.51 @ 780nm

Numerical Aperture NA:
0.55

Substrate: D-ZLaF52LA
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 4.95
f#: 0.91
Bevel: Protective bevel as needed
Connector: FC/PC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 9.6
Lightpath Lens Code: 355230
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Lens Included: #87-154
Alignment Wavelength (nm): 633

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant