

TECHSPEC® 6.35mm Dia. x 12.7mm EFL, UV Enhanced Aluminum 50Å 90° Off-Axis Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#37-289** ☒ In Stock

[Other Coating Options](#)

1 **C\$266.00**

ADD TO CART

Qty 1-5

C\$266.00

Qty 6+

C\$239.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
6.35 +0.1/-0.0

Effective Focal Length EFL (mm):
12.70

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 12.70
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 6.35
Surface Figure, RMS: λ/8
Surface Roughness (Angstroms): <50 RMS
Wavelength Range (nm): 250 - 700
Surface Quality: 80-50
Compatible Mounting Plates: #37-943
Substrate: Aluminum 6061-T6
Y Offset (mm): 12.70
Reflected Wavefront, RMS: λ/4

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View