

671nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#64-255** **1 In Stock**

☐ [Additional Bandwidths](#)

-

1

+

C\$1,337⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,337.00 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter

Type:

Physical & Mechanical Properties

25.00 +0.0/-0.1

Diameter (mm):

≥22

Clear Aperture CA (mm):

±0.10

Thickness Tolerance (mm):

Mounted in Black Anodized Ring	Construction:
ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	Physical Durability:
2.0 ±0.1	Substrate Thickness (mm):
Optical Properties	
0 ±2	Angle of Incidence (°):
2.6	Bandwidth (nm):
<11	Beam Deviation (arcsec):
540 - 643 & 678 - 961	OD 5 Blocking Wavelength Range (nm) :
617 - 661 & 681 - 738	OD 6 Blocking Wavelength Range (nm):
≥6.0	Optical Density OD (Average):
671.00	Center Wavelength CWL (nm):
671	Design Wavelength DWL (nm):
2.55 - 4.7	Full Width-Half Max FWHM (nm):
Fused Silica	Substrate: □
>90	Minimum Transmission (%):
Hard Coated	Coating:
60-40	Surface Quality:
>90	Transmission (%):
540 - 643 & 678 - 961	Blocking Wavelength Range (nm):
¼ @ 633nm	Transmitted Wavefront, P-V:
Threading & Mounting	
3.5 ±0.1	Mount Thickness (mm):
Environmental & Durability Factors	
<5	Temperature Dependence (ppm/°C):
ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	Environmental Durability:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts