

TECHSPEC®

6.0mm Diameter x 72.0mm FL, 1064nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#69-593** ☒ In Stock

☐ [Other Coating Options](#)

1

C\$62.30

ADD TO CART

Qty 1-9

C\$62.30

Qty 10+

C\$56.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

72.00 @ 587.6nm
Back Focal Length BFL (mm): 70.97
Coating: Laser V-Coat (1064nm)
Coating Specification: R _{abs} <0.25% @ 1064nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.60 ±0.05
Edge Thickness ET (mm): 1.48
Radius R₁ (mm): 37.22
Clear Aperture CA (mm): 5.4
f/#: 12.00
Numerical Aperture NA: 0.04
Design Wavelength DWL (nm): 1064
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant