

6.8mm Dia. x 6mm FL, NIR I Coated, Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#15-879** ☐ **In Stock**

[Other Coating Options](#)

-

1

+

C\$78.40

ADD TO CART

Qty 1-10
C\$78.40
Qty 11+
C\$69.30
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.80 +/-0.3

Effective Focal Length EFL (mm):
6.00 @ 587.6nm

Numerical Aperture NA:
0.56

Back Focal Length BFL (mm): 4.20
Substrate:  Liba2000+
Focal Length Tolerance (%): ±5
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 5.44
Edge Thickness ET (mm): 0.65
Center Thickness CT (mm): 2.80 ±0.20
f#: 0.9
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 6.8
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant