

TECHSPEC® 6° Nom. Uncoated, N-BK7 Wedge Prism



Stock **#45-556** ☐ In Stock

1

C\$66.50

ADD TO CART

Qty 1-5
C\$66.50
Qty 6+
C\$53.20
Volume Pricing
Request Quote

Get Product Downloads



Coating:

Uncoated

Angle Tolerance (arcsec):

±30

Bevel:

Protective bevel as needed

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

7.1
Design Wavelength DWL (nm): 632.8
Diameter (mm): 25.00 +0.00/-0.10
Image Orientation: Beam Deviation
Power (diopters): 10.51
Ray Deviation @ 633nm (°): 6.00
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 3.00
Type: Wedge Prism
Wavelength Range (nm): 350 - 2200
Wedge Angle: 11° 21'
Maximum Edge Thickness (mm): 8.0

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View