

TECHSPEC® 6.25mm Dia. x 10mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-689-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 + **C\$107.80**

ADD TO CART

Qty 1-5
C\$107.80
Qty 6+
C\$86.10
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 ±0.025

Effective Focal Length EFL (mm):
10.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 7.83
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 5.625
Centering (arcmin) : <3
Center Thickness CT (mm) : 4.09 ±0.10
Center Thickness CT 1 (mm) : 3.06 ±0.05
Center Thickness CT 2 (mm) : 1.03 ±0.05
Radius R₁ (mm) : 6.98
Radius R₂ (mm) : -4.35
Radius R₃ (mm) : -41.01
Edge Thickness ET (mm) : 3.23
Substrate : ☐ N-BAF10 / N-SF10
Surface Quality : 40-20
f/# : 1.6
Numerical Aperture NA : 0.31
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View