

TECHSPEC® 6.25mm Dia. x 17.5mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-949** ☐ In Stock
[Other Coating Options](#)

1 **C\$100.80**

ADD TO CART

Qty 1-5
C\$100.80
Qty 6+
C\$80.50
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):
17.50

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 15.46
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 5.625
Centering (arcmin) : <1
Center Thickness CT (mm) : 3.75 ±0.10
Center Thickness CT 1 (mm) : 2.75 ±0.05
Center Thickness CT 2 (mm) : 1.00 ±0.05
Radius R₁ (mm) : 11.13
Radius R₂ (mm) : -9.22
Radius R₃ (mm) : -38.49
Edge Thickness ET (mm) : 3.18
Substrate: ☐ N-SSK6 / N-SF56
Surface Quality : 40-20
f/# : 2.8
Numerical Aperture NA : 0.18
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View