

632.8nm, 1mW Fiber-Coupled Frequency Stabilized Laser Diode



632.8nm Frequency Stabilized Laser Diodes (Free Space and Fiber-Coupled options shown)

Stock **#73-776** 1 In Stock

-

1

+

C\$11,200^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$11,200.00 each
Need More?	Request Quote

Product Downloads



General

2.00

Warm-Up Time (minutes):

Single Mode w/3mm Dia Stainless Steel Shielding

Fiber Cable Type:

Diode

Type of Laser:

IIIb

Laser Class - CDRH:

Physical & Mechanical Properties

71.0 L x 63.5 W x 19.8 H	Dimensions (mm):
135.00	Weight (g):

1	Length of Fiber (m):
<50 (8 Hours)	Pointing Stability (μrad):

Optical Properties

0.13	Numerical Aperture NA:
4.3 MFD	Fiber Diameter (μm):

632.80	Wavelength (nm):
±0.5	Wavelength Tolerance (nm):

±0.002	Beam Stability (nm):
Red	Color:

<100	Spectral Line Width (KHz):
------	----------------------------

Electrical

1	Output Power (mW):
1.00	Power Stability (%):

Max: 5	Power Consumption (W):
±20	Output Power Tolerance (%):

10 Hz - 100 MHz 0.2% RMS	Noise Level:
Max: 2 @ 3.3 V	Input Current (A):

Hardware & Interface Connectivity

10-pin Connectors (cable provided upon request)	Electrical Leads/ Pin Connections:
USB	Computer Interface:

Fiber-Coupled	Output Type:
FC/APC	Connector:

Environmental & Durability Factors

+15 to +40	Operating Temperature (°C):
5 - 95% (non-condensing)	Operating Humidity:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Single Longitudinal Mode (SLM) Performance
- ±0.002nm Wavelength Stability
- Very Low Power Consumption

632.8nm Frequency Stabilized Laser Diodes are ideal for typical HeNe laser applications including flow cytometry, interferometry, confocal microscopy, fluorescence excitation, and Raman spectroscopy. Whereas a comparable HeNe laser would be larger, more expensive, and consume more power, the 632.8nm Frequency Stabilized Laser Diodes feature more compact designs, ±0.002nm wavelength stability, and either greater than 60mW power (free-space model) or greater than 20mW power (fiber coupled model). Additionally, these lasers utilize Variable Bragg Gratings (VBG) to lock the 632.8nm wavelength to a 10MHz linewidth.