

TECHSPEC® 648nm CWL, 12.5mm Dia, 14nm Bandwidth, OD 6 Fluorescence Filter



Stock **#33-335** ☐ In Stock

-

1

+

C\$348.60

ADD TO CART

Qty 1-5
C\$348.60
Qty 6+
C\$289.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.10

Angle of Incidence (°):
0 ±5

Bandwidth (nm):
14.00

OD 6 Blocking Wavelength Range (nm):

300 - 621 & 677 - 925

Optical Density OD (Average):
≥6.0

Clear Aperture CA (mm):
8.69

Center Wavelength CWL (nm):
648.00

Full Width-Half Max FWHM (nm):
20.00

Substrate: 
[BOROFLOAT®](#)

Minimum Transmission (%):
93

Coating:
Hard Coated

Surface Quality:
60-40

Thickness Tolerance (mm):
±0.1

Transmission (%):
93.00

Type:
Bandpass Filter

Blocking Wavelength Range (nm):
250 - 1100

Construction:
Mounted in Black Anodized Ring

Transmitted Wavefront, RMS:
λ/4 (prior to coating)

Compatible Fluorophore:
FITC Emission

Environmental Durability:
Humidity per MIL-STD-810H, Section 507.6
Temperature per MIL-STD-810H, Section 501.7 and 502.7

Physical Durability:
Adhesion per MIL-PRF-13830B, Section C.4.5.12
Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11
Cleaning per MIL-C-48497ASection 4.5.4.2

Mount Thickness (mm):
3.5 ±0.1

Substrate Thickness (mm):
2.00 ±0.25

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)