

[See all 245 Products in Family](#)

TECHSPEC[®] 6mm Dia. x 6mm FL, UV-AR Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#49-246** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

 C\$207²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$207.20 each
Qty 6-25	C\$165.20 each
Qty 26-49	C\$156.80 each
Need More?	Request Quote

Product Downloads

General

Double-Convex Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

6.00 +0.0/-0.025	
Centering (arcmin):	<1
Bevel:	Protective as needed
Center Thickness CT (mm):	4.10 ±0.05
Edge Thickness ET (mm):	1.97
Clear Aperture CA (mm):	5.4

Optical Properties	
Back Focal Length BFL (mm):	4.38
Effective Focal Length EFL (mm):	6.00
Coating:	UV-AR (250-425nm)
Coating Specification:	R _{abs} ≤1.0% @ 250 - 425nm R _{avg} ≤0.75% @ 250 - 425nm R _{avg} ≤0.5% @ 370 - 420nm
Substrate: ☐	Fused Silica (Corning 7980)
Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4
Radius R ₁ =R ₂ (mm):	4.76
f/#:	1.00
Focal Length Specification Wavelength (nm):	587.6
Focal Length Tolerance (%):	±1
Numerical Aperture NA:	0.50
Wavelength Range (nm):	250 - 425
Damage Threshold, Reference: ☐	3 J/cm² @ 355nm, 10ns



Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 235:	Compliant

Product Details

- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma
- Precision Fused Silica Substrate





TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.




Technical Information



UV FS Transmission Curve

FUSED SILICA																									
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>92</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table> Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data	Wavelength (nm)	Transmission T (%)	200	92	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90	
Wavelength (nm)	Transmission T (%)																								
200	92																								
400	94																								
600	94																								
800	94																								
1000	94																								
1200	94																								
1400	92																								
1600	94																								
1800	94																								
2000	94																								
2200	90																								
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for MgF2 Coated Fused Silica</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>96</td></tr><tr><td>600</td><td>96</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1200</td><td>95</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>95</td></tr><tr><td>1800</td><td>95</td></tr><tr><td>2000</td><td>95</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table> Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	Wavelength (nm)	Transmission T (%)	200	94	400	96	600	96	800	95	1000	95	1200	95	1400	93	1600	95	1800	95	2000	95	2200	90	
Wavelength (nm)	Transmission T (%)																								
200	94																								
400	96																								
600	96																								
800	95																								
1000	95																								
1200	95																								
1400	93																								
1600	95																								
1800	95																								
2000	95																								
2200	90																								
Fused Silica with UV-AR Coating Typical Transmission <table border="1"><caption>Approximate data for UV-AR Coated Fused Silica</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>250</td><td>99</td></tr><tr><td>300</td><td>99</td></tr><tr><td>400</td><td>99</td></tr><tr><td>500</td><td>98</td></tr><tr><td>600</td><td>90</td></tr><tr><td>800</td><td>78</td></tr><tr><td>1000</td><td>76</td></tr><tr><td>1200</td><td>77</td></tr></tbody></table> Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	Wavelength (nm)	Transmission T (%)	200	70	250	99	300	99	400	99	500	98	600	90	800	78	1000	76	1200	77					
Wavelength (nm)	Transmission T (%)																								
200	70																								
250	99																								
300	99																								
400	99																								
500	98																								
600	90																								
800	78																								
1000	76																								
1200	77																								

Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$ $R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with YAG-BBAR Coating	

Typical Transmission 	Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 532nm $R_{abs} \leq 0.25\%$ @ 1064nm $R_{avg} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\%$ @ 750 - 800nm $R_{abs} \leq 1.0\%$ @ 800 - 1550nm $R_{avg} \leq 0.7\%$ @ 750 - 1550nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts