

TECHSPEC® 6mm Dia. x 9mm FL, NIR II Coated, Achromatic Lens



Stock **#45-783** ☐ In Stock

1 **C\$142.80**

ADD TO CART

Qty 1-5

C\$142.80

Qty 6+

C\$114.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):
9.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 6.66
Focal Length Specification Wavelength (nm) : 880.00
Clear Aperture CA (mm) : 5.4
Centering (arcmin) : <3
Center Thickness CT (mm) : 5.30 ±0.10
Center Thickness CT 1 (mm) : 4.00 ±0.05
Center Thickness CT 2 (mm) : 1.30 ±0.05
Radius R₁ (mm) : 7.34
Radius R₂ (mm) : -4.18
Radius R₃ (mm) : -11.58
Edge Thickness ET (mm) : 4.26
Substrate : 
Surface Quality : 40-20
f/# : 1.5
Numerical Aperture NA : 0.33
Coating : NIR II (750-1550nm)
Coating Specification : R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 750 - 1550

Regulatory Compliance

RoHS 2015 : Compliant
Reach 224 : Compliant
Certificate of Conformance : View