

[See all 195 Products in Family](#)

TECHSPEC® 6mm Diameter x 18mm FL, 1064nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCXLenses

Stock **#87-941** **5 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ C\$264⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$264.60 each
Qty 6-25	C\$212.80 each
Qty 26-49	C\$194.60 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

6.00 +0.00/-0.05 **Diameter (mm):**

Centering (arcmin):

<1

Center Thickness CT (mm):
2.00 ±0.05

Edge Thickness ET (mm):
1.44

Clear Aperture CA (mm):
5.4

Bevel:
Protective as needed

Optical Properties

Effective Focal Length EFL (mm):
18.00 @ 587.6nm

Back Focal Length BFL (mm):
16.62

Coating:
Laser V-Coat (1064nm)

Coating Specification:
 $R_{\text{abs}} < 0.25\%$ @ 1064nm

Substrate:
[Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Power (P-V) @ 632.8nm:
 λ

Irregularity (P-V) @ 632.8nm:
 $\lambda/10$

Focal Length Tolerance (%):
 ± 1

Radius R_1 (mm):
8.25

f#:
3.00

Numerical Aperture NA:
0.17

Design Wavelength DWL (nm):
1064

Damage Threshold, By Design:
 15 J/cm^2 @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details


- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- $\lambda/10$ Surface Accuracy

TECHSPEC® Laser Grade PCXLenses are designed for high energy Nd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring $\lambda/10$ surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCXLenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.


LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information



1064nm V-Coat
 $R_{(abs)} < 0.25\% @ 1064nm$



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts