

[See all 12 Products in Family](#)

## 700µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-746 **NEW** 1 In Stock

- 1 + C\$259.<sup>00</sup>

**ADD TO CART**

|                |                               |
|----------------|-------------------------------|
| Volume Pricing |                               |
| Qty 1+         | C\$259.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### Physical & Mechanical Properties

|              |                               |
|--------------|-------------------------------|
| 25.4         | Outer Diameter (mm):          |
| 700 ± 5.0    | Fixed Aperture Diameter (µm): |
| 0.06 ± 0.004 | Thickness (inches):           |
| 1.52         | Thickness (mm):               |
| ±0.1         | Thickness Tolerance (mm):     |

## Optical Properties

Low Reflective Chrome

Coating:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10 $\mu$ m to 1,000 $\mu$ m

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10 $\mu$ m to 1000 $\mu$ m. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.