

[See all 32 Products in Family](#)

750 - 900nm (Ti:Sapphire), 4-6mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- π Shaper_TiS_Q-5

See More by [AdlOptica](#)



Stock **#25-849** **1 In Stock**

1 C\$4,914.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$4,914.00 each
Qty 5+	C\$4,368.00 each
Need More?	Request Quote

Product Downloads

General

Focal- π Shaper_TiS_Q-5 **Model Number:**

Beam Shaper **Type:**

#12-322

Compatible Adapter:

Physical & Mechanical Properties

29.00	Length (mm):
50	Weight (g):
20	Clear Aperture CA (mm):
42.00	Diameter (mm):
2.5 - 4	Input Beam Diameter, $1/e^2$ (mm):

Optical Properties

>99	Transmission (%):
750, 900	Design Wavelength DWL (nm):
750 - 900	Wavelength Range (nm):
TEM ₀₀	Input Beam Mode:
<1.5	Typical Input Beam Mode Quality, M ² :
±20	Input Beam Divergence (mrad):

Electrical

0.2	Maximum Input Power, CW (kW):
-----	-------------------------------

Threading & Mounting

M30 x 0.75	Inner Thread:
M30 x 0.75	Outer Thread:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica piShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal- π Shaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal- π Shapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information



