

TECHSPEC®

75.0mm Dia. x 150.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#45-370** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$133.00

ADD TO CART

Qty 1-9
C\$133.00
Qty 10+
C\$119.70
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.025

Effective Focal Length EFL (mm):
150.00 @587.6nm

Back Focal Length BFL (mm): 142.45
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 11.45 ±0.10
Edge Thickness ET (mm): 1.78
Radius R₁ (mm): 77.52
Clear Aperture CA (mm): 73.5
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View