



[See all 5 Products in Family](#)

Everix Ultra-Thin OD 2 Longpass Filter, 700nm, 12.5mm Square

See More by [Everix](#)



Stock **#35-127** CLEARANCE **7 In Stock**

- 1 + C\$103⁶⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$103.60 each
Qty 11+	C\$93.24 each
Need More?	Request Quote

Product Downloads

General	
Flexible Filter	Type:
Physical & Mechanical Properties	
12.5 x 12.5	Dimensions (mm):
	Length (mm):

12.50	
	Width (mm):
12.50	
	Dimensional Tolerance (mm):
±0.1	
	Clear Aperture (%):
>90	
Optical Properties	
	Optical Density OD (Average):
2.0 (absolute)	
	Cut-On Wavelength (nm):
700.00	
	Transmission (%):
>85 (average)	
	Cut-On Tolerance (%):
±3 typical	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	

Product Details

- Ultra-Thin, Flexible Substrate
- Sharp Cut-On Wavelength Designs
- Extruded Thin Film, Insensitive to Scratches

Everix Ultra-Thin Longpass Filters combine high performance and low cost in a new class of thin film interference filters that are flexible, scratch insensitive, and ultra-thin (200 - 500µm). These filters feature cut-on wavelengths in the visible range with cut-on tolerances of ±3% typical and >85% average transmission. The flexible extruded thin film filters are complex multilayer filters, which excel across a variety of needs, including longpass, edge, and notch filters. Everix Ultra-Thin Longpass Filters are ideal for demanding vision and medical technology applications.

Note: Custom filter designs can be purchased directly from [Everix](#).

Technical Information

