

TECHSPEC®

75mm Square Uncoated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock **#48-415** 20+ In Stock

-

1

+

C\$154<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$154.00 each                |
| Qty 6-25       | C\$123.20 each                |
| Qty 26-99      | C\$116.20 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

60.00

#Sorting:

General

Protective Window

Type:

Physical & Mechanical Properties

70.00 x 70.00

Clear Aperture CA (mm):

|                      |                             |
|----------------------|-----------------------------|
| 75.00 x 75.00        | Dimensions (mm):            |
| 3.00                 | Thickness (mm):             |
| 75.00                | Length (mm):                |
| 75.00                | Width (mm):                 |
| ±0.25                | Dimensional Tolerance (mm): |
| Protective as needed | Bevel:                      |
| Fine Ground          | Edges:                      |
| 0.22                 | Poisson's Ratio:            |
| 71.5                 | Young's Modulus (GPa):      |
| 500.00               | Knoop Hardness (kg/mm²):    |

Optical Properties

|            |                                        |
|------------|----------------------------------------|
| Uncoated   | Coating:                               |
| B270       | Substrate: □                           |
| 1.523      | Index of Refraction (n <sub>d</sub> ): |
| 60-40      | Surface Quality:                       |
| 58.3       | Abbe Number (v <sub>d</sub> ):         |
| 360 - 2700 | Wavelength Range (nm):                 |
| 1λ         | Surface Flatness (P-V):                |

Material Properties

|                     |                                                              |
|---------------------|--------------------------------------------------------------|
| 2.56                | Density (g/cm³):                                             |
| 9.4 (+20 to +300°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 247:                  |

## Product Details

- Large Selection of Sizes
  - Available Uncoated, MgF2, or VIS-NIR Anti-Reflection (AR) Coated
  - Custom Sizes Available for Volume OEM Requirements
- TECHSPEC® B270 Windows offer a high transmission from the visible to the near-infrared (NIR). They have a similar refractive index to N-BK7 while being more cost-effective. These windows are often used as a protective element due to their high solarization stability and chemical resistance, making them ideal for standard window applications. TECHSPEC® B270 Windows are available either uncoated or coated with a MgF2 or VIS-NIR Anti-Reflection (AR) Coating. Both circular and square options are offered in various sizes, and custom sizes and coatings are available for OEM applications.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---