

76.2mm Dia., 6mm Thick, Uncoated,  $\lambda$ /10 IR Fused Silica Window



Stock **#70-111** 20+ In Stock

-

1

+

C\$1,001<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$1,001.00 each              |
| Qty 6-25       | C\$798.00 each                |
| Qty 26-49      | C\$749.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

68.58

Clear Aperture CA (mm):

76.20 +0.00/-0.20

Diameter (mm):

|                      |                          |
|----------------------|--------------------------|
| 6.00 ±0.10           | Thickness (mm):          |
| Protective as needed | Bevel:                   |
| 90                   | Clear Aperture (%):      |
| Fine Ground          | Edges:                   |
| <5                   | Parallelism (arcsec):    |
| 0.16                 | Poisson's Ratio:         |
| 73                   | Young's Modulus (GPa):   |
| 522.00               | Knoop Hardness (kg/mm²): |

|                       |                                        |
|-----------------------|----------------------------------------|
| Optical Properties    |                                        |
| Uncoated              | Coating:                               |
| IR Fused Silica       | Substrate: □                           |
| 1.458                 | Index of Refraction (n <sub>d</sub> ): |
| 20-10                 | Surface Quality:                       |
| λ/10 per inch over CA | Transmitted Wavefront, P-V:            |
| 67.8                  | Abbe Number (v <sub>d</sub> ):         |
| 200 - 3500            | Wavelength Range (nm):                 |

|                                                             |                                                              |
|-------------------------------------------------------------|--------------------------------------------------------------|
| Material Properties                                         |                                                              |
| 2.20                                                        | Density (g/cm³):                                             |
| 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| <a href="#">View</a>  | Certificate of Conformance: |

## Product Details

- IR Grade Fused Silica Substrates
- Broad Transmission Range from 200 – 3500nm
- λ/10 Transmitted Wavefront Distortion
- Excellent Thermal Stability

λ/10 Infrared (IR) Fused Silica Windows feature 20-10 surface quality, <5 arcsec parallelism, and broad transmission from 200 – 3500nm without absorption bands common in other fused silica materials. These fused silica windows offer superior transmission characteristics and a low coefficient of thermal expansion that provides high thermal stability and resistance to thermal shock. λ/10 Infrared (IR) Fused Silica Windows feature laser grade specifications and are available in a variety of diameter and thickness options. These windows are ideal for FLIR, FTIR spectroscopy, medical systems, and thermal imaging applications.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).