

766.5nm CWL, 50mm Dia.,High Transmission Traditional Coated 10nm Bandpass Filter



High Transmission Traditional Coated Bandpass Filters

Stock **#71-716** **1 In Stock**

-

1

+

C\$770⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$770.00 each
Qty 11-25	C\$654.50 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter

Type:

Physical & Mechanical Properties

50.00 +0/-0.25

Diameter (mm):

45.0

Clear Aperture CA (mm):

Thickness (mm):

5.90	
	Construction:
Mounted in Black Anodized Ring	
Optical Properties	
	Center Wavelength CWL (nm):
766.50	
	Center Wavelength CWL Tolerance (nm):
+2/-0	
	Full Width-Half Max FWHM (nm):
10.00	
	Full Width-Half Max FWHM Tolerance (nm):
±2	
	Minimum Transmission (%):
80	
	Coating:
Traditional Coated	
	Blocking Wavelength Range (nm):
1x10 ⁻⁴ avg Xray to 1200nm	

Environmental & Durability Factors	
	Operating Temperature (°C):
-50 to +70	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	REACH 241:
Compliant	

Product Details

- Passband Transmission up to 80%
- 441.6 to 1064nm Wavelength Options with 10, 20, and 40nm Bandwidths
- Ideal for Medical and Analytical Applications

High Transmission Traditional Coated Bandpass Filters are designed for situations where far-infrared blocking is not required, allowing for up to 80% transmission in the passband region and good blocking over the visible and NIR wavelength range. Featuring popular laser, mercury, biomedical, and analytical spectral lines, these filters cover a wide range of visible and NIR wavelengths. A hermetic seal and an anodized metal mount help maintain performance in high humidity environments and protect against chipping and scratching. High Transmission Traditional Coated Bandpass Filters are ideal for a range of scientific and medical applications such as spectral radiometry, medical diagnostics, chemical analysis, and Colorimetry. For applications requiring wider blocking ranges, [traditional coated bandpass filters](#) are available whereas applications requiring higher transmission above 90% are best served with [hard coated bandpass filters](#).